



# ESSILOR PALs RANGE AVAILABILITY

Accolade Freedom™ (MFH 17-15 mm)	Power Range	Index	Base Curves	Diameter	Add Power
1.50 Index Plastic	+6.00 D to -10.00 D	1.50	2.00, 3.00, 4.50, 6.00, 7.00	Blank size available as finished uncut	0.75 to 3.50
1.50 Index Plastic Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.50	2.00, 3.00, 4.50, 6.00, 7.00		0.75 to 3.50
Airwear®	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50		0.75 to 3.50
Airwear® Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50		0.75 to 3.50
Airwear® Xperio™ (Gray/Brown)	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50		0.75 to 3.50
Thin&Lite® 1.60	+6.00 D to -10.00 D	1.60	2.00, 3.00, 4.00, 5.50, 6.50		0.75 to 3.50
Thin&Lite® 1.60 Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.60	2.00, 3.00, 4.00, 5.50, 6.50		0.75 to 3.50
Thin&Lite® 1.67	+8.00 D to -12.00 D	1.67	2.00, 3.00, 4.00, 5.50, 6.50, 8.00		0.75 to 3.50
Thin&Lite® 1.67 Transitions® VI (Gray/Brown)	+8.00 D to -12.00 D	1.67	2.00, 3.00, 4.00, 5.50, 6.50, 8.00		0.75 to 3.50
Thin&Lite® 1.74	+8.00 D to -12.00 D	1.74	2.00, 3.00, 4.00, 5.50, 6.50, 8.00		0.75 to 3.50
Trivex® Available Q4 2009	+6.00 D to -10.00 D	1.53	2.00, 3.00, 4.50, 6.00, 7.00	0.75 to 3.50	
<b>Accolade® (MFH 17 mm)</b>					
1.50 Index Plastic	+6.00 D to -10.00 D	1.50	2.00, 3.00, 4.50, 6.00, 7.00	80/85 mm	0.75 to 3.50
1.50 Index Plastic Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.50	2.00, 3.00, 4.50, 6.00, 7.00	77/82 mm	0.75 to 3.50
Airwear®	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50	80/85 mm	0.75 to 3.50
Airwear® Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50	78/83 mm	0.75 to 3.50
Airwear® Xperio™ (Gray/Brown)	+6.00 D to -10.00 D	1.59	2.00, 3.00, 4.00, 5.50, 6.50	76/81 mm	0.75 to 3.50
Thin&Lite® 1.60	+6.00 D to -10.00 D	1.60	2.00, 3.00, 4.00, 5.50, 6.50	78/83 mm	0.75 to 3.50
Thin&Lite® 1.60 Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.60	2.00, 3.00, 4.00, 5.50, 6.50	78/83 mm	0.75 to 3.50
Thin&Lite® 1.67	+8.00 D to -12.00 D	1.67	2.00, 3.00, 4.00, 5.50, 6.50, 8.00	75/80 mm 70/75 mm	0.75 to 3.50
Thin&Lite® 1.67 Transitions® VI (Gray/Brown)	+8.00 D to -12.00 D	1.67	2.00, 3.00, 4.00, 5.50, 6.50, 8.00	78/83 mm 73/78 mm	0.75 to 3.50
Thin&Lite® 1.74	+8.00 D to -12.00 D	1.74	2.00, 3.00, 4.00, 5.50, 6.50, 8.00	Uncut	0.75 to 3.50
Trivex® Available Q4 2009	+6.00 D to -10.00 D	1.53	2.00, 3.00, 4.50, 6.00, 7.00	79/84 mm	0.75 to 3.50
<b>Ovation® (MFH 17 mm)</b>					
1.50 Index Plastic	+6.00 D to -10.00 D	1.50	1.75, 3.00, 4.50, 6.00, 7.00	80/85 mm	0.75 to 3.50
1.50 Index Plastic Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.50	1.75, 3.00, 4.50, 6.00, 7.00	77/82 mm	0.75 to 3.50
Airwear®	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	80/85 mm	0.75 to 3.50
Airwear® Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	78/83 mm	0.75 to 3.50
Airwear® Xperio™ (Gray/Brown)	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	75/80 mm	0.75 to 3.50
Thin&Lite® 1.67	+8.00 D to -12.00 D	1.67	1.75, 3.00, 4.50, 5.50, 6.50, 8.00	78/83 mm 73/78 mm	0.75 to 3.50
Thin&Lite® 1.67 Transitions® VI (Gray)	+8.00 D to -12.00 D	1.67	1.75, 3.00, 4.50, 5.50, 6.50, 8.00	78/83 mm 73/78 mm	0.75 to 3.50



## Accolade Freedom

- Faster adaptation
- Freedom in your choice of frames
- Reduced distortion
- Enhances visual fields, providing more natural vision

## Accolade

- Faster adaptation
- Allows wider acuity fields for myopes
- Provides softer periphery for hyperopes
- Balances natural vision for low ametropes

## Ovation

- Customized design to specific Rx
- Eliminates annoying distortions
- Accommodates wearer's prescription for comfortable reading

\*Cylinder on all products is -4.00 D



# ESSILOR PALs RANGE AVAILABILITY

	Power Range	Index	Base Curves	Diameter	Add Power
<b>SmallFit® (MFH 14 mm)</b>					
1.50 Index Plastic	+6.00 D to -10.00 D	1.50	1.75, 3.00, 4.50, 6.00, 7.00	80/85 mm	0.75 to 3.00
1.50 Index Plastic Transitions® VI (Gray)	+6.00 D to -10.00 D	1.50	1.75, 3.00, 4.50, 6.00, 7.00	77/82 mm	0.75 to 3.00
Airwear®	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	75/80 mm	0.75 to 3.00
Airwear® Transitions® VI (Gray/Brown)	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	74/79 mm	0.75 to 3.00
Airwear® Xperio™ (Gray/Brown)	+6.00 D to -10.00 D	1.59	1.75, 3.00, 4.50, 5.50, 6.50	75/80 mm	0.75 to 3.00
Thin&Lite® 1.60	+6.00 D to -10.00 D	1.60	1.75, 3.00, 4.50, 5.50, 6.50	78/83 mm	0.75 to 3.00
Thin&Lite® 1.67	+8.00 D to -12.00 D	1.67	1.75, 3.00, 4.50, 5.50, 6.50, 8.00	78/83 mm 73/78 mm	0.75 to 3.00
Thin&Lite® 1.67 Transitions® VI (Gray/Brown)	+8.00 D to -12.00 D	1.67	1.75, 3.00, 4.50, 5.50, 6.50, 8.00	78/83 mm 73/78 mm	0.75 to 3.00
<b>Essilor Natural® (MFH 18 mm)</b>					
1.50 Index Plastic	+6.00 D to -10.00 D	1.50	1.75, 3.75, 5.50, 6.50, 7.50	80/85 mm	0.75 to 3.50
1.50 Index Plastic Transitions® VI (Gray)	+6.00 D to -10.00 D	1.50	1.75, 3.75, 5.50, 6.50, 7.50	77/82 mm	0.75 to 3.50
Airwear®	+6.00 D to -10.00 D	1.59	1.75, 3.75, 5.50, 7.25	80/85 mm	0.75 to 3.00
Airwear® Transitions® VI (Gray)	+6.00 D to -10.00 D	1.59	1.75, 3.75, 5.50, 7.25	78/83 mm	0.75 to 3.00
Thin&Lite® 1.60	+6.00 D to -10.00 D	1.60	2.00, 4.00, 5.50, 7.25	78/83 mm 73/78 mm	0.75 to 3.50
1.60 High Index Glass	+6.00 D to -7.50 D	1.60	3.50, 5.25, 6.75	70/75 mm	0.75 to 3.50
1.60 High Index PhotoGray Extra®	+6.00 D to -7.50 D	1.60	3.50, 5.25, 6.75	70/75 mm	0.75 to 3.50
<b>Adaptar® (MFH 18 mm)</b>					
1.50 Index Plastic	+7.00 D to -10.00 D	1.50	2.25, 4.25, 6.25, 8.25, 5.00	80 mm 80/85 mm	0.75 to 3.50
1.50 Index Plastic Transitions® VI (Gray)	+7.00 D to -10.00 D	1.50	2.25, 4.25, 6.25, 8.25, 5.00	77 mm 77/82 mm	0.75 to 3.50
Airwear®	+6.50 D to -10.00 D	1.59	2.25, 4.25, 5.50, 7.25	80/85 mm	1.00 to 3.00
Clear Glass	+6.00 D to -10.00 D	1.53	2.00, 4.00, 6.00, 8.00	70/75 mm	0.75 to 3.50
PhotoGray Extra® Glass	+6.00 D to -10.00 D	1.53	2.00, 4.00, 6.00, 8.00	70/75 mm	0.75 to 3.50

\*Cylinder on all products is -4.00 D



## SmallFit

- Provides wearers a greater choice of small frame designs
- Customized to wearer's prescription and addition
- Soft design provides comfortable intermediate vision

## Essilor Natural

- Balances increased add power, delivering greater comfort and clarity
- Offers a wide near zone, minimizing unnatural head movement
- Aids in reducing the "swim" effect

## Adaptar

- Optimum peripheral clarity and wearer comfort
- Easy adaptation for every stage of presbyopia

